



**INVACARE® PLATINUM 10  
OXYGEN CONCENTRATOR**



**Yes, you can.®**

The **Invacare® Platinum™ 10 Oxygen Concentrator** is designed to provide an alternative to liquid systems and is known for reliability and performance. The 10 liter unit features quiet operation, a top handle and bottom recesses for easy handling and a side filter access door. In addition, the concentrator is compatible with the Invacare® HomeFill® Oxygen System and is available with an **Invacare® SensO<sub>2</sub>® Oxygen Purity Sensor**.

### Features

Self diagnostic electronics designed to minimize troubleshooting time.  
 Top handle for ease of mobility.  
 Battery-free power loss alarm, Invacare® Sieve-GARD™ Monitor helps protect sieve from degradation, compressor 35 psi pressure-relief valve and low flow alarm.


### Provider Benefits

Designed to provide continuous flow up to 10 liters per minute as an alternative to liquid systems.  
 All Platinum 10 stationary concentrators include a HomeFill system port for inventory flexibility.  
 Patient-accessible reset button helps minimize emergency service calls.

### Patient Benefits

User friendly design with easy to see control panel, humidifier bottle holder and filter access.  
 HomeFill system compatibility allows patients with flow rates up to 5LPM to enjoy life's experiences with small, refillable cylinders.  
 Reliable concentrator provides unlimited, worry-free oxygen supply.

### HCPCS Code: E1390\*



1. Invacare® HomeFill® Oxygen System connection
2. Easy to maintain filter
3. Also available with Invacare® SensO<sub>2</sub>® Oxygen Purity Sensor



**Hitwin Healthcare Pvt. Ltd.**  
 7/10, Jaganathan Nagar  
 2nd Main Road,  
 Arumbakkam,  
 Chennai,  
 India - 600106.  
**Ph: 91 44 4684 5555**  
**: 91 44 4233 3313**

**Invacare Corporation**  
 www.invacare.com

**USA**  
 One Invacare Way  
 Elyria, Ohio  
 44035-4190  
 (800) 333-6900

**Canada**  
 570 Matheson Blvd. E.,  
 Unit 8  
 Mississauga, Ontario  
 L4Z 4G4 Canada  
 (800) 668-5324

©2019  
 Invacare Corporation.  
 All rights reserved.  
 Trademarks are identified by the symbols™ and®.  
 All trademarks are owned by or licensed to Invacare Corporation unless otherwise noted. Lotus is a registered trademark of Inovo, Inc. Specifications are subject to change without notification.  
 Form No. 19-134  
 190832

Model #	Dimensions	Weight	Shipping Weight	Quantity	Oxygen Flow	Flow Range	Maximum Outlet Pressure	Pressure Relief Mechanism
IRC10LX	26 3/8" H	54 lb.	60 lb.	1 Per Case	10 LPM	2-10 LPM	9+/- 0.5 PSI	35 PSI
IRC10LXO2	18 3/8" W 14 3/8" D			18 Per Pallet				+/- 5 PSI

O <sub>2</sub>	Filter	Electrical Requirements	Rated Current Input	Average Power Consumption	Sound Level	Limited Warranty
Oxygen Purity	Filter	Electrical Requirements	Rated Current Input	Average Power Consumption	Sound Level	Limited Warranty
94%-87% At All Flow Rates	Cabinet Compressor Inlet, Outlet HEPA	120 VAC +/- 10%, 60 Hz (132VAC/108VAC)	4.9 A	585 W	≤ 58 db (A)	3 Years

\*All references to HCPCS codes: Providers are responsible for determining the appropriate billing codes when submitting claims to the Medicare program, and should consult an attorney or other advisor to discuss specific situations in further detail.

