

An ISO 9001: 2008 Certified Company

::: CCD WHEEL ALIGNER ::: :: Model :- WA 350 ::



:: TECHNICAL DETAILS ::

Item	Measurement Precision	Measurement Range
Total toe	±4' (±0.02°)	±10 ⁰
Individual toe	±2' (±0.01°)	±5 ⁰
Camber	±2' (±0.01°)	±15 ⁰
Castor	±6′ (±0.1°)	±20 ⁰
SAI / KPI	±6' (±0.1°)	±20 ⁰
Setback	±2′ (±0.03°)	±6 ⁰
Thrust angle	±2' (±0.03°)	±6 ⁰
Electrical power	220v, 1ph	
Cabinet color	Red / Blue	
Weight	200kg	
Packing size	1. 1000x750x1400mm	
_	2. 825x600x1100mm	





An ISO 9001: 2008 Certified Company

:: MAIN FUNCTIONS & FEATURES ::

- 1. Three kind of measurement mode can be selected.
- 2. Complete test: The Wheel Aligner can be used to measure the most wheel alignment parameters, such as front wheel toe-in, front wheel camber, caster, Kingpin inclination, rear wheel toe-in, rear wheel camber, thrust angle, wheelbase difference, tread difference, axle offset, front wheel setback and rear wheel setback, etc.
- 3. Complete databank: wheel alignment data of over 20,000 vehicle models is stored in the system. User can also add new data to the databank.
- 4. Adopts the charge coupled device (CCD) with high resolution, infrared 8-beam and full loop measurement, accurate and stable, wireless communication mode
- 5. Based on the thrust line to realize the real alignment measurement.
- 6. Front alignment test function: user can select the alignment mode flexibly. Only two probe rods are mounted can the emergency alignment measurement for the front wheels be performed.
- 7. The sensor heads are individually interchangeable. After changing one of the sensor heads, the other three needs not to recalibrate, which makes the after-sales service more convenient.
- 8. Fully intellect. The system can automatically recognize the vehicle with super-low chassis to perform the alignment test for this kind of vehicle and the vehicle with enclosed housing. Aiming to the vehicle model, the system can automatically turn on the corresponding functions of height measurement and counterweight, etc.
- 9. The demonstration version can run all test flow, which makes user's training more convenient and quick.
- 10. The units of the alignment parameters can be represented with Degree/Minute, percentage degree, mm and Inch.